



# PRODUCT SHEET COLUMNS

## **Standard size**

### **2 mL Columns (Polypropylen - PP)**

**Order N°: AC-141-AL**

- Empty columns
- Bag of 100 columns, including 100 frits<sup>1</sup> (polyethylene - PE) and 100 caps-(PP)
- Luer<sup>2</sup> connection at column outlet
- Column outlet sealed with breakable tip

Also available prepacked with resin<sup>3</sup>.

### **Dimensions :**

**Internal diameter:** 7 mm

**Filling height of resin :** > 39 mm

**External diameter of column outlet (Luer):** 4 mm

**Internal diameter of column outlet (Luer):** ~2 mm



### **Accessories for 2 mL columns**

#### **1/ 20 mL funnel (PP)**

**Order N°: AC-120**, bag of 20

### **Dimensions :**

**Upper diameter :** 25 mm

**Height :** 78 mm

**Volume :** up to 25 mL



---

<sup>1</sup> Frits : pore size = 30µm

<sup>2</sup> Luer : standard type connection

<sup>3</sup> Available with the following resins : AC, LN, NI, PB, RE, SR, TEVA, TRU, UTEVA in boxes of :

- 20 units (C20)

- 50 units (C50)

- 200 units (C200 corresponding to 4x C50)



## PRODUCT SHEET COLUMNS

### 2/ Column closure caps

Order N°: AC-130, bag of 100

For capping 2mL standard columns for storage



### 3/ Rack 12 positions - Plexiglas

Order N°: AC-104

Numerated positions (1 to 12)

Racks can be staggered for sequential separations

#### Dimensions :


**Height :** 128 mm

**Length :** 475 mm

**Width :** 120 mm

**Height beneath single rack :** 122 mm

**Height between 2 staggered racks :** 115 mm



### 4/ Rack 15 positions - acrylic


Order N°: AC-103

#### Dimensions :

**Height :** 160 mm

**Length :** 240 mm

**Width :** 115 mm



### 5mL Columns (PP)

Order N°: AC-50E-5M

- Only available as empty columns
- Bag of 50 columns, including 50 frits (PE) and 50 caps (PP)
- Luer<sup>2</sup> connection at column outlet
- Column outlet closed with cap

#### Dimensions :

**Internal diameter :** 90-95 mm

**Filling height of resin :** up to 8 cm

**External diameter of column outlet (Luer):** 4 mm

**Internal diameter of column outlet (Luer):** ~2 mm



# PRODUCT SHEET COLUMNS

## 20mL Columns (PP)

Order N°: AC-20E-20M

- Only available as empty columns
- Bag of 20 columns, including 20 frits (PE) and 20 caps (PP)
- Luer<sup>2</sup> connection at column outlet
- Column outlet closed with red cap

### Dimensions :

Internal diameter : 15 mm

Filling height of resin : up to 10 cm

External diameter of column outlet (Luer): 4 mm

Internal diameter of column outlet (Luer): ~1.5 mm



## Accessories for 20 mL columns

### 250 mL funnel (PP)

Order N°: AC-20X-20M, Bag of 20

### Dimensions :

Upper diameter : 63 mm

Height : 150 mm

Volume : up to 250 mL



## ***Columns available on request : 5, 8 et 10 mL***

Pre-packed columns (PP) in boxes of 20 units, available for SR, TEVA, TRU and UTEVA resin :

Order N°:

SR5-C20-A, SR8-C20-A, SR10-C20-A

TE5-C20-A, TE8-C20-A, TE10-C20-A

TR5-C20-A, TR8-C20-A, TR10-C20-A

UT5-C20-A, UT8-C20-A, UT10-C20-A

- Luer<sup>2</sup> connection at column outlet
- Column outlet sealed with breakable tip

### Dimensions :

Internal diameter : 14 mm

Volumes : 5 mL resin

8 mL resin

10 mL resin

